

geemarc™ AMPLIDECT400BT

Hear the Difference

Amplified Cordless Telephone with Bluetooth



CALLING/TALKING

- Bluetooth connectivity to Bluetooth enabled Hearing Aids
- Adjustable receiving volume : up to 30dB with boost
- Adjustable receiving tone (treble, standard, bass) +/-10dB
- Speaker phone / hands free
- Redial, pause, flash, mute
- Phonebook up to 50 numbers (12 characters, 20 digits)
- Redial function for last 10 outgoing calls
- Choice of 7 languages (English, French, German, Dutch, Italian, Spanish and Portuguese)
- 4 one-touch memories keys
- 1 SOS memory key
- Auto answer

HANDSET LCD DISPLAY

- Navigational menu
- Clock
- Alarm
- Key lock
- Message waiting icon

CALLER ID *

- Type 1, type 2
- FSK / DTMF
- Caller ID also for Call waiting

RINGER

- Extra loud ringer (85dB)
- 10 melodies
- Adjustable ring volume (5 positions)
- Special ring option for 10 numbers
- Vibration ON/OFF selectable

MULTI HANDSET

- 3-way conference with privacy protection
- Up to 4 bases and up to 5 handsets
- Call transfer of external calls (when using several handsets)

TECHNICAL SPECIFICATIONS

- 3 batteries ni-Mh 1.2V 600mA
- Standby time : 5 days
- Continuous talk time : 6 hours
- P/T dialing mode
- Torch function
- GAP compliant
- Outdoor range 300 meters
- Indoor Range 50 meters
- 2.5mm socket
- Wall mountable
- Size :22 x 16 x 10.5 cm

OPTIONAL EXTRA

- Headset (CLA3)
- CLHook 1,5,6
- Inductive neckloop (CLA7)