

Ken

## Enhanced Cordless Phone

Ken

- Powerful and adjustable volume
- Clear, high quality sound that makes your conversation easy and enjoyable
- Adjustable boosted ringer volume to ensure you don't miss a call
- Flash notification on headset for incoming calls so you can see when the phone is ringing
- Vibrating notification on handset so that you can feel incoming calls
- Clear, stylish design that makes the phone easy to use
- Package includes power supply, docking station and Silhouette telecoil ear hook for direct to the hearing aid transmission in "T" or "MT" mode (ear hook is included in certain packages and can be ordered separately)



Manufactured by:  **Phonic Ear**<sup>®</sup>  
Connected to life

Kongebakken 9 • 2765 Smørum • Denmark  
Phone: +45 3917 7101 • Fax: +45 3927 7900  
E-mail: mail@phonicear.com



For more information visit  
[www.phonicear.com](http://www.phonicear.com)

Your local representative:



Boosted volume  
Vibrating alert  
Flash alert



92 1-30-710-00 Rev. A 0307

© 2007 Phonic Ear A/S

For more information visit [www.phonicear.com](http://www.phonicear.com).

# Xen

## MultiSens



- Boosted volume
- Vibrating alert
- Flash alert



# Xen

Xen incorporates cordless phone technology with stylish, intelligent design for ease of use, and features that assist those with reduced hearing. Notification of an incoming call is made through vibration, light and an adjustable boosted ringer. This means that the phone can be adjusted to your needs ensuring that important phone calls from friends and family are not missed. As Xen is cordless it can be taken with you around the home and garden so you no longer have to rush to answer a call. The enhanced features mean conversations are clear, relaxed and enjoyed by you, your family and friends.

Actual size



- Powerful, adjustable speaker to ensure conversations are clear.
- Backlit display that increases character size and visibility.
- Boosts volume to maximum level quickly and easily so both non-hearing impaired and hearing impaired can use the phone. Raised detail on the button makes it possible to feel the boost button during a call.
- Setup your phone to your specific needs including vibration and flash alerting.
- Answer or make a call using this centrally located clearly marked button.
- High contrast between the phone, button and printed numbers and letters making it easy to read and use.
- Two raised areas on the number 5 button assist users to feel and be orientated around the keypad.
- Quick access to recently dialled numbers allowing them to be redialled quickly.
- Speaker volume can be incrementally adjusted depending on the surroundings, callers voice and your hearing.